



S9480

15PAR38/LED/40'/RED/120V
15 watt PAR38 LED; Red; 40' beam spread; Medium base; 120 volts

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- IP65 - Wet location rated
- Approved for enclosed fixtures
- For Indoor and Outdoor use
- ABS Lens
- Dimmable



S9480

| Item Number | UPC | Voltage | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | | |
|-----------------------|--|----------------|----------------|------------------|----------------------------|--------------------------------|--------------------------|--|--|
| S9480 | 045923094804 | 120 | 15 | PAR38 | Medium | E26 | 15PAR38/LED/40'/RED/120V | | |
| Dimmable/Non-Dimmable | Suggested Dimmers | Finish | MOL In Inches | MOD In Inches | Average Rated Hours | Color | Beam Spread Deg | | |
| Dimmable | Compatible dimmers for S9480 | Silver | 5-3/16" | 4-3/4" | 25000 | Red | 40 | | |
| Pack | Package Type | RoHS Compliant | Fixture Type | UL or ETL Listed | UL Classification | Warranty | | | |
| 12/6 | Box | Yes | Enclosed Rated | Yes | cULus - Wet Location Rated | 3 Year Limited | | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

