

Contour Series High CRI PAR20 2700K, 460lm LED Lamp with 40-Degree Beam Angle

- 90 CRI - Renders illuminated colors with great accuracy
- LED replacement for 50W halogen lamps
- 2700K - soft white
- 40-degree beam angle
- Compatible with most commercial dimmers*
- Energy efficient, long-lasting LED - over 80% reduction in energy costs compared to halogen lamps
- 25,000 hour design lifetime
- 5-year limited warranty

* Dimming range may vary based on dimmer used.



Specifications	
Lamp Type	High CRI PAR20 2700K, 460lm, 40-degree beam angle
Model	P20-L460-C27-B40-90-W
Part Number	98827
Color Temperature	2700K
Lumen Output	460lm
Wattage	7W
Replacement Equivalent	50W Halogen equivalent
CRI	90
Efficacy	66lm/W
Beam Angle	40°
CBCP	593 cd
Dimmable	Yes
Wet Rated?	Yes
Voltage	120V
Operating Temperature	-20°C to +40°C
Base	E26
Weight	3.9 oz.
Dimensions	2.47 x 3.25 x 2.47 in
Design life	25000 Hours
Warranty	5-Year Limited Warranty

Certifications:




Contour Series High CRI PAR20 2700K, 460lm LED Lamp with 40-Degree Beam Angle

Additional Images:



Diagrams:



Lighting Facts:

Lighting Facts Per Bulb Information concernant l'éclairage Pour une ampoule	
Brightness/Luminosité	460 lumens
Estimated Yearly Energy Cost Estimation Des Coûts Énergétiques Annuels	\$0.84
<small>Based on 3 hrs/day, 11¢/kWh Sur la base de 3 heures / jour, 11 ¢ / kWh Cost depends on rates and use Le coût dépend du tarif et de l'utilisation</small>	
Life/Durée de vie	22.8 years/années
<small>Based on 3 hrs/day Sur la base de 3 heures/jour</small>	
Light Appearance/Degré de luminosité	
<small>Warm/Chaude Cool/Froide</small>	
2700K	
Energy Used/Energie utilisée	7 watts