



S9566

6.5G40/CL/LED/E26/27K/120V
 6.5 watt G40 LED; Clear; Medium base; 2700K; 810 lumens;
 120 volts

Features

- LED with a traditional incandescent look and feel
- Omni-directional light source
- Smooth dimming
- Replaces up to 60 watt lamps
- Long life - 15,000 hours
- Damp Location
- UL listed for totally enclosed fixtures
- Shatterproof option available on request



S9566

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S9566	045923095665	120	6.5	60W	>0.70	G40	Medium

ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches	Initial Lumens
E26	6.5G40/CL/LED/E26/27K/120V	Dimmable	Compatible dimmers for S9566	Clear	6-1/2"	4-7/8"	810

Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type
15000	2700	Warm White	80	360	-20C (-4F) to a maximum of +45C (+113F)	12/6	Box

CEC Status	RoHS Compliant	UL or ETL Listed	UL Classification	Warranty
Non-Compliant	Yes	Yes	cULus - Damp Location Rated	3 Year Limited