

F3002/5ORBH: 5 - Light Chandelier



Dimensions:

Diameter:	25 1/2"	Overall Height:	92 1/4"
Height:	26 3/4"	Wire:	180" (color/Brown)
		Chain:	60"
		Mounting Proc.:	Center Lock-Up
		Connection:	Mounted To Box

Bulbs:

5 - Medium A19 75w Max. 120v - Not included

Features:

•

Material List:

1 Body - Steel - Oil Rubbed Bronze with Highlights

Safety Listing:

Safety Listed for Dry Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (F3001-3_F3002-5)

Collection: Standish

UPC #: 014817538083

Finish: Oil Rubbed Bronze with Highlights (ORBH)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Glass	Glass	White Opal Etched	5									

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	F3002/5ORBH	1	014817538083	27	14.4	26.8	6.03	19	250	Yes
NJ Pallet		9		48	40	72.25	80.278	171		No
NV Pallet		9		48	40	71.5	79.444	169.2		No