



# 9350-HLK



VIDEO

## Product Description

4" dia. round fixture support box for use with nonmetallic sheathed cable

**Brand:** fiberglassBOX™  
**Catalog #:** 9350-HLK

**Carton Quantity:** 50  
**Carton Weight:** 27 lb.

**Width:** 4 in.  
**Depth:** 2-7/16 in.  
**Volume:** 22.5 cu. in.  
**Type of Installation:** New Work  
**Round Ceiling Box**

**UPC:** 085339620945  
**UNSPSC:** 39121316  
**Country of Origin:** United States of America

## FEATURES

Machine tapped fixture holes, rigid hard box construction, no distortion with high temperatures, shatter resistant with low temperatures, Speed "K" Clamps factory installed

## APPLICATION

New work residential construction 2 HR fire resistive walls and ceilings (50 lbs. fixture support)

## STANDARDS

ANSI / UL 514C: File No. E30594



## FIRE CLASSIFICATION

### Fire Test of Building Construction Materials

ANSI / UL 263: File No. CEYY.R9379 (Category / File No.)

*Note: Products must also be certified to: ANSI / UL 514C*

### Fire Resistance Classification in Wall Assemblies 2-Hours or less

Shall be separated by a horizontal distance of not less than 3 inches

### Fire Resistance Classification in Floor-Ceiling Assemblies 2-Hours or Less

Distance between boxes in adjacent cavities may be reduced to 5 1/2 inches

*Note: For more details please refer to the UL fire resistive directory and Allied Moulded's CEYY.9379 (Outlet boxes and fittings classified for fire resistance)*

## COLOR

Beige/tan

## MATERIAL

Fiberglass reinforced polyester BMC

## MOUNTING

Nail-on backside HN hanger bracket for adjusting to additional wall/ceiling substrate

## ADDITIONAL MATERIALS

Galvanized steel brackets and plated carbon steel fasteners

Polyvinyl chloride clamps

## SUPPORT RATING

50 lbs fixture support