



65625-962: One Light Pendant



Collection: Wheaton

Downlight Pendant in Brushed Nickel Finish with Satin Etched Glass Shade

UPC #:785652656354

Finish: Brushed Nickel (962)

Dimensions:

Diameter: 15 1/4"

Height: 12 1/2"

Weight: 6.7 lbs.

Overall Height: 135"

Wire: 144" (color/Clear)

Chain: 120"

Mounting Proc.: Center Lock-Up

Connection: Mounted To Box

Bulbs:

- 1 - Medium A19 150w Max. 120v - Not included
- 1 - LED Medium A19 8w Max. 120v - Not included
- 1 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- A decorative canopy is included
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.
- Supplied with wire pre-laced through chain

Material List:

- 1 Body - Steel - Brushed Nickel
- 1 Chain - Steel - Brushed Nickel

Safety Listing:

- Safety Listed for Dry Locations
- Safety Listed for Dry Locations

Instruction Sheets:

- English (HC-1563)
- French (F-004)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Satin Etched	1				5 7/8	15 1/4	1 3/4			

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	1 1/8			5 1/2		

Replacement Bulb Data:

Product #		Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted	A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted	A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted	A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted	A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
--------------	-----------	----------	-----	--------	-------	--------	------	--------	-----------	----------

Individual	65625-962	1	785652656354	18	17.75	9.75	1.803	8.4	150	Yes
NJ Pallet		36		48	40	75	83.333	302.4		No
NV Pallet		36		48	40	75	83.333	302.4		No