

Item #: 12424-2	UPC Code: 747396802039
Product Family Name:	Finish: Gold Leaf
Category: Table Lamp	Category Type: Table Lamp
Certification E341302	
Patents	
Notes:	



Image File Name:
12424-2--
1509558028.jpg



MEASUREMENTS

Width: 15	Length: 15	Height: 26.5	Extension:
Height Adjustable: No	Min Overall Height:	Max Overall Height:	Slope: No
Wire Length: 96	Chain Length:	Safety Cable Included: No	Net Weight: 5.29
Canopy Width:	Canopy Height:	Canopy Length:	
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:

LAMPING

No. of Bulbs: 1	Light Type: A-19,Med			
Max Bulb Wattage: 100	Socket: E26, Medium			
Dimmable: No	Ballast:	Rated Life Hours:	Photocell Included: N	Lamps Included: No
Lamp Included: No	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:

SHADE / GLASS

Description:	Material: Fabric
Part No.: RS12424-2	Quantity: 1
Width: 15.00	Height: 10.00
	Length: 15.00



SHIPPING

Carton Width: 21.500	Carton Height: 11.250	Carton Length: 23.000
Carton Weight: 9.020	Carton Cubit Feet: 3.219	Small Package Shippable: Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		Master Pack: 1



UL Listed

Yes