

Item #:	UPC Code:
12422-0	747396092263
Product Family Name:	Finish:
	Polished Nickel with Mercury Glass
Category:	Category Type:
Table Lamp	Table Lamp
Certification:	
E341302	
Patents:	
Notes:	
E26 CFL 13W Bulb*1PC	



Image File Name:
12422-0--
1509557931.jpg



MEASUREMENTS

Width:	Length:	Height:	Extension:
16		28	
Height Adjustable:	Min Overall Height:	Max Overall Height:	Slope:
No			No
Wire Length:	Chain Length:	Safety Cable Included:	Net Weight:
96		No	6.53
Canopy Width:	Canopy Height:	Canopy Length:	
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:

LAMPING

No. of Bulbs:	Light Type:			
1	A-19, Medium			
Max Bulb Wattage:	Socket:			
100	E26, Medium			
Dimmable:	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included:
No			N	No
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
No				

SHADE / GLASS

Description:	Material:	
	Fabric	
Part No.:	Quantity:	
RSA12422		
Width:	Height:	Length:
16.00	10.00	



SHIPPING

Carton Width:	Carton Height:	Carton Length:	
24.000	11.000	25.000	
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:	
11.088	3.819	Yes	
Master Pack Width:	Master Pack Height:	Master Pack Length:	
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:	Master Pack:
			1



UL Listed

Yes