



LED54WPT50KMOG-G5



Description LED Litespan Post Top 54W 6480lm 5K 80+CRI Non-Dim
120-277V E39 Universal Burn Position

Ordering Code 09028

UNSPSC Code 39112102

Specifications

Voltage Rating	100~277
Voltage Type	AC
Watts	54
Amps	0.666
mA	666
Lumens per Watt	120
Base Type	Mogul Screw (E39)
MOL in/mm	10.67/271
MOD in/mm	3.65/92.8
Lumens	6480
CT deg K	5000
CRI	80+
Beam Angle	360°
Rated Life	50,000
Special Desc	MIN.LAMP COMPARTMENT DIMENSIONS (L) 400mm by (W) 400mm
Replaces	175-250W HID
Ambient Operating Temp Range	-30° C (-22° F) to 60° C (140° F)

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335