

MINKA-LAVERY®

Item #: 3301-84	UPC Code: 747396097435
Product Family Name: Poleis	Finish: Brushed Nickel
Category: Mini-Pendants	Category Type: Mini Pendant
Certification 3057374	
Patents	
Notes:	



Image File Name:
3301-84--
1475632808.jpg



MEASUREMENTS

Width: 3.75	Length: 3.75	Height: 9.25	Extension: 3.75
Height Adjustable: Yes	Min Overall Height: 20.00	Max Overall Height: 56.00	Slope: Yes
Wire Length: 72"	Chain Length: 72"	Safety Cable Included: No	Net Weight: 4.32
Canopy Width: 5.50	Canopy Height: 1.13	Canopy Length: 5.50	
Backplate Width: 3.75	Backplate Height: 6.25	Center to Top: 3.75	Center to Bottom: 3.75

LAMPING

No. of Bulbs: 1	Light Type: T-10,Med			
Max Bulb Wattage: 60	Socket: E26,Medium			
Dimmable: Yes	Ballast: Yes	Rated Life Hours: 10000	Photocell Included: N	Lamps Included: No
Lamp Included: No	Color Temp.: 2700K	CRI: 90	Initial Lumens: 1600	Delivered Lumens: 1600

SHADE / GLASS

Description: G3301	Material: Glass
Part No.:	Quantity: 1
Width: 3.75	Height: 6.25
	Length: 3.75



SHIPPING

Carton Width: 7.250	Carton Height: 7.750	Carton Length: 13.250
Carton Weight: 5.104	Carton Cubic Feet: 0.431	Small Package Shippable: Yes
Master Pack Width: 13.750	Master Pack Height: 16.500	Master Pack Length: 15.250
Master Pack Weight: 21.248	Master Cubic Feet: 3.500	Multi-Pack: 4



ETL Intertek

Yes