

Blo dweLED™ LED Ceiling and Wall FM-11

WAC LIGHTING Responsible Lighting®



Fixture Type:

Catalog Number:

Project: _____

Location: _____

PRODUCT DESCRIPTION

Multiple mid-powered LEDs illuminate the acrylic diffuser uniformly without socket shadows which are common in conventional flush mounts.

FEATURES

- Energy Star® rated
- Damp location listed
- CSA listed
- ADA compliant
- Wall or Ceiling Mount
- Translucent acrylic diffuser
- Multiple LED array for uniform illumination
- 120VAC - no driver needed
- Smooth and continuous ELV dimming
- 85 CRI
- 100% - 10% dimming
- 36,000 hour rated life
- 5 year warranty

SPECIFICATIONS

Construction: Aluminum with white acrylic diffuser

Input: 120VAC

Harmonic Distortion (THD): 20%

Operating Temperature: -35°C (-31°F) to 50°C (122°F)

ORDERING NUMBER

		Watt	Color Temp	LED Lumens (Without diffuser)	Delivered Lumens (With diffuser)	Finish
	FM-113	22W	27 2700K	1695	1395	WT White
			35 3500K	1770	1510	
	FM-115	33W	27 2700K	2475	2060	WT White
			35 3500K	2595	2150	

FM - - - WT

Example: **FM-113-35-WT**

wacighting.com
Phone (800) 526.2588
Fax (800) 526.2585

Headquarters/Eastern Distribution Center
44 Harbor Park Drive
Port Washington, NY 11050

Central Distribution Center
1600 Distribution Ct
Lithia Springs, GA 30122

Western Distribution Center
1750 Archibald Avenue
Ontario, CA 91760