

6TL DRY TAPE 24V COLLECTION

6T 20' 2700K 24V Standard Output Dry LED Tape Black

6T120H27BK (Black Material (Not Painted))

Project Name: _____
Location: _____
Type: _____
Qty: _____
Comments: _____



Certifications/Qualifications

Class 2	Yes
Location Rating	CSA UL Listed Dry
	www.kichler.com/warranty

Dimensions

Length	240.00"
Width	0.50"

Mounting/Installation

Interior/Exterior	Interior
-------------------	----------

Photometrics

Color Rendering Index	90
Delivered Lumens	210
Kelvin Temperature	2700K

Primary Lamping

Dimmable	Yes
Expected Life Span	50000
Lamp Included	Integrated
Light Source	LED



Product/Ordering Information

SKU	6T120H27BK
Finish	Black
Style	Other
UPC	783927497039

Specifications

Material	PCB
----------	-----

Additional Finishes

-  Black Material (Not Painted)
-  White Material (Not Painted)

Kichler

7711 East Pleasant Valley Road Cleveland, Ohio 44131-8010
Toll free: 866.558.5706 or kichler.com

Notes:

- 1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.
- 2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.

KICHLER®