



S9135

10BR30/LED/4000K/830L/120V/D
 Discontinued - 10 watt; BR30 LED; 108° beam spread; 4000K;
 Medium base; 120 volts; Dimmable

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable



S9135

This item has been discontinued.
 Possible replacement:

- [S9622](#)

Item Number	Product Line	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape
S9135	DiTTO	045923091353	120	10	65W	0.99	BR30

Base	ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches
Medium	E26	10BR30/LED/4000K/830L/120V/D	Dimmable	Compatible dimmers for S9135	Frosted	5-3/16"	3-3/4"

Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type
830	25000	4000	Cool White	80	108	12/6	Box

RoHS Compliant	UL or ETL Listed	UL Classification	Warranty	Status	Suggested Substitute
Yes	Yes	Damp	3 Year Limited	Discontinued	S9622



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

