



GE  
Lighting

### 39074 - GE High Lumen Blax

**LED172G11/835/10**

☞ Instant/PS Ballast

☞ Indoor Applications

### Product Photo



### GENERAL CHARACTERISTICS

Base Description	2G11 Plug-In
Base Type	Plug-in
Body Color	White
Dimmable	No
Product Color	White
Product Technology	LED
Rated Life (Hours)	40000 h
Dimmable / Non-Dimmable	No
Lamp Count	10
Life in Years	36.5 yr
Replacement Watts	0 W
Requested Structure	Case Pack
Estimated Energy Cost per Year	2.05
Base	2G11
Bulb Shape	HLBX

### PHOTOMETRIC CHARACTERISTICS

Lumens per Watt (Efficacy)	123.5 lm
Nominal Initial Lumen per Watt	123.5
Initial Lumens-nominal	2150 lm
Color Rendering Index-CRI	80
Color Temperature	3500 K

### PRODUCT INFORMATION

Product Code	39074
Description	LED172G11/835/10
Alternative Unit Of Measure	CASE
Standard Package Quantity	10
Ean UPC	043168390743
Standard Package GTIN	10043168390740
No Of Items Per Sales Unit	
No Of Items Per Standard Package	10
Sales Unit	Case
UCC	043168390743
Alternative Unit Of Measure	EACH
Standard Package Quantity	10
Ean UPC	043168390743
Standard Package GTIN	00043168390743
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
Sales Unit	Each
UCC	043168390743

### DIMENSIONS

Bulb Max Overall Length-MOL	22.3 in
-----------------------------	---------

### ELECTRICAL CHARACTERISTICS

Rated power (Watts)	17 W
---------------------	------