

2 ft. x 2 ft. 4000K, 40W LED Edge Lit Flat Panel

- 2 ft. x 2 ft. size - easily fits into standard T-bar grid ceilings
- High efficacy - 100 lm/W
- High efficiency, dimmable driver (0-10V)
- Uniform, glare-free light evenly distributed over entire panel
- Light Guide Plate utilizing high purity Mitsubishi PMMA maximizes transparency and efficiency
- Lightweight and ultra-thin (less than 2 in. thick) - easily replace existing fixtures
- Surface mount kit available (sold separately)
- High quality construction with smooth welds. Impact resistant, easy to clean
- Durable and attractive white powder-coat finish
- WAGO connectors included for simple daisy chain wiring
- 4000K - Cool White
- 120-277V input voltage
- 50,000 hour rated lifetime
- 5-year limited warranty



| Specifications | |
|-----------------------|--------------------------|
| Lamp Type | 2 ft. x 2 ft. 4000K, 40W |
| Model | PN22-W40-C40-010 |
| Part Number | 99297 |
| Color Temperature | 4000K |
| Lumen Output | 4000lm |
| Wattage | 40W |
| Power Factor | 0.95 |
| CRI | 80 |
| Efficacy | 100lm/W |
| Dimmable | 0-10V |
| Voltage | 120-277V |
| Operating Temperature | -20°C to +40°C |
| Weight | 131.2 oz. |
| Dimensions | 23.70 x 1.83 x 23.70 in |
| Rated Lifetime | 50000 Hours |
| Warranty | 5-Year Limited Warranty |
| DLC Product Listing | PN22-W40-C40-010 |

Certifications:



2 ft. x 2 ft. 4000K, 40W LED Edge Lit Flat Panel

Diagrams:

