



- ◆ Industrial Quality
- ◆ Special Tungsten Carbide Tip
- ◆ Copper / Silver Brazing
- ◆ Special Flute Design Improves Penetration without Blow Back or Compacting
- ◆ Fastest Dust Removal
- ◆ Fastest Drilling Speeds
- ◆ Heat Treated Body
- ◆ Clean Round Holes
- ◆ Less Vibration
- ◆ Polished Finish
- ◆ ANSI Specification

- Brick
- Stone
- Masonry
- Aggregates



BARCODED

SOLD INDIVIDUALLY.
1 PER CLIP.

715Sxxxxx-B
Bulk Pack/Tube



SDS-PLUS - Bohr Hammer

Part #	Size	X	O/A	Drilling	Head	Qty	List
715S41064	5/32"	X	4-1/2"	2"	4-PLUS	1	\$5.97
715S61064	5/32"	X	6-1/4"	4"	4-PLUS	1	\$6.81
715S61064-B	5/32"	X	6-1/4"	4"	4-PLUS	25	\$161.74
715S41264	3/16"	X	4-1/2"	2"	4-PLUS	1	\$5.97
715S41264-B	3/16"	X	4-1/2"	2"	4-PLUS	25	\$141.79
715S61264	3/16"	X	6-1/4"	4"	4-PLUS	1	\$6.81
715S61264-B	3/16"	X	6-1/4"	4"	4-PLUS	25	\$161.74
715S81264	3/16"	X	8-1/4"	6"	4-PLUS	1	\$9.42
715S81264-B	3/16"	X	8-1/4"	6"	4-PLUS	25	\$223.73
715S10316	3/16"	X	10"	8"	4-PLUS	1	\$12.50
715S12316	3/16"	X	12"	10"	4-PLUS	1	\$15.50
715S14316	3/16"	X	14"	12"	4-PLUS	1	\$22.59
715S16316	3/16"	X	16"	14"	4-PLUS	1	\$29.66
715S41464	7/32"	X	4-1/2"	2"	4-PLUS	1	\$6.99
715S61464	7/32"	X	6-1/4"	4"	4-PLUS	1	\$7.22
715S81464	7/32"	X	8-1/4"	6"	4-PLUS	1	\$8.97
715S11732	7/32"	X	11"	9"	4-PLUS	1	\$16.21
715S16732	7/32"	X	16"	14"	4-PLUS	1	\$26.21
715S41664	1/4"	X	4-1/2"	2"	4-PLUS	1	\$5.97
715S41664-B	1/4"	X	4-1/2"	2"	4-PLUS	25	\$141.79
715S61664	1/4"	X	6-1/4"	4"	4-PLUS	1	\$6.81
715S61664-B	1/4"	X	6-1/4"	4"	4-PLUS	25	\$148.44
715S81664	1/4"	X	8-1/4"	6"	4-PLUS	1	\$8.97
715S81664-B	1/4"	X	8-1/4"	6"	4-PLUS	25	\$213.04
715S11014	1/4"	X	11"	9"	4-PLUS	1	\$11.45
715S14014	1/4"	X	14"	12"	4-PLUS	1	\$22.45
715S16014	1/4"	X	16"	14"	4-PLUS	1	\$24.22
715S20014	1/4"	X	20"	18"	4-PLUS	1	\$29.04
715S62064	5/16"	X	6-1/4"	4"	4-PLUS	1	\$8.31
715S62064-B	5/16"	X	6-1/4"	4"	4-PLUS	25	\$197.36
715S82064	5/16"	X	8-1/4"	6"	4-PLUS	1	\$11.02
715S12516	5/16"	X	12"	10"	4-PLUS	1	\$20.75
715S62464	3/8"	X	6-1/4"	4"	4-PLUS	1	\$9.03
715S62464-B	3/8"	X	6-1/4"	4"	4-PLUS	25	\$214.46
715S82464	3/8"	X	8-1/4"	6"	4-PLUS	1	\$10.42
715S10038	3/8"	X	10-1/4"	8"	4-PLUS	1	\$14.61
715S12038	3/8"	X	12-1/4"	10"	4-PLUS	1	\$18.53
715S12038-B	3/8"	X	12-1/4"	10"	4-PLUS	25	\$176.04
715S18038	3/8"	X	18"	16"	4-PLUS	1	\$26.72
715S24038	3/8"	X	24"	22"	4-PLUS	1	\$34.39
715S62864	7/16"	X	6-1/4"	4"	4-PLUS	1	\$12.44
715S10716	7/16"	X	10-1/4"	8"	4-PLUS	1	\$17.56
715S12716	7/16"	X	12-1/4"	10"	4-PLUS	1	\$19.56
715S18716	7/16"	X	18"	16"	4-PLUS	1	\$29.33
715S63264	1/2"	X	6-1/4"	4"	4-PLUS	1	\$10.39
715S63264-B	1/2"	X	6-1/4"	4"	4-PLUS	25	\$246.76
715S10012	1/2"	X	10-1/4"	8"	4-PLUS	1	\$17.93
715S12012	1/2"	X	12-1/4"	10"	4-PLUS	1	\$19.56
715S12012-B	1/2"	X	12-1/4"	10"	4-PLUS	10	\$185.82
715S12018	1/2"	X	18"	16"	4-PLUS	1	\$24.02
715S12024	1/2"	X	24"	22"	4-PLUS	1	\$44.10



SDS-PLUS - Bohr Hammer

Part #	Size	X	O/A	Drilling	Head	Qty	List
715S63664	9/16"	X	6-1/4"	4"	4-PLUS	1	\$16.10
715S10916	9/16"	X	10-1/4"	8"	4-PLUS	1	\$20.79
715S12916	9/16"	X	12-1/4"	10"	4-PLUS	1	\$24.15
715S18916	9/16"	X	18"	16"	4-PLUS	1	\$27.60
715S64064	5/8"	X	6-1/4"	4"	4-PLUS	1	\$12.83
715S84064	5/8"	X	8"	6"	4-PLUS	1	\$18.43
715S84064-B	5/8"	X	8"	6"	4-PLUS	10	\$175.09
715S12058	5/8"	X	12"	10"	4-PLUS	1	\$26.72
715S18058	5/8"	X	18"	16"	4-PLUS	1	\$38.19
715S24058	5/8"	X	24"	22"	4-PLUS	1	\$47.21
715S14464	11/16"	X	12"	10"	REGULAR	1	\$35.75
715S84864	3/4"	X	8"	6"	REGULAR	1	\$23.72
715S84864-B	3/4"	X	8"	6"	REGULAR	10	\$225.34
715S10034	3/4"	X	10"	8"	REGULAR	1	\$29.26
715S12034	3/4"	X	12"	10"	REGULAR	1	\$34.61
715S12034-B	3/4"	X	12"	10"	REGULAR	5	\$164.40
715S18034	3/4"	X	18"	16"	REGULAR	1	\$46.35
715S24034	3/4"	X	24"	22"	REGULAR	1	\$60.67
715S85664	7/8"	X	8"	6"	REGULAR	1	\$41.59
715S85664-B	7/8"	X	8"	6"	REGULAR	5	\$197.55
715S10078	7/8"	X	10"	8"	REGULAR	1	\$44.48
715S12078	7/8"	X	12"	10"	REGULAR	1	\$46.93
715S12078-B	7/8"	X	12"	10"	REGULAR	5	\$222.92
715S18078	7/8"	X	18"	14"	REGULAR	1	\$52.01
715S86464	1"	X	8"	6"	REGULAR	1	\$46.24
715S10001	1"	X	10"	8"	REGULAR	1	\$51.88
715S10001-B	1"	X	10"	8"	REGULAR	5	\$246.43
715S12001	1"	X	12"	10"	REGULAR	1	\$54.72
715S18001	1"	X	18"	16"	REGULAR	1	\$73.33
715S22018	1-1/8"	X	10"	8"	X-CUTTER	1	\$89.60
715S24014	1-1/4"	X	18"	16"	X-CUTTER	1	\$99.11




3 Head Styles:

Depending on diameter, different carbide tips offer advantages:




4-PLUS

A new, fast, & tough carbide tip provides long life, easy centering, and fast drilling through all aggregates, concrete, masonry, brick, stone, and rebar if straight on.



REGULAR

Traditional Tungsten Carbide Tip with Copper Silver Brazing for clean drilling through all aggregates, concrete, masonry, brick, & stone. Regular heads are found on SDS-PLUS sizes over 5/8".



X-CUTTER

4 Sided Traditional Tungsten Carbide Tip with Copper Silver Brazing for *Super Fast* clean drilling through all aggregates, concrete, masonry, brick, & stone. Will not cut rebar!

