

### APPLICATIONS

Introducing the Mobern VW-LED Premium grade enclosed and gasketed vaportight fixture. This Energy-Saving High Performance LED Vaportight is ideal for both indoor and outdoor applications where dust and water resistance is required. Ideal for parking garages, cold storage, marinas, barns, canopies, car washes, poultry farms, agricultural applications and other areas susceptible to corrosive and wet conditions.

### FEATURES & BENEFITS

- ◆ Designed for easy assembly
- ◆ Ease of Installation and Maintenance
- ◆ Visually familiar light sourcing
- ◆ Poured in place gasket seals the enclosures from most hostile environments
- ◆ Economical Mounting System can provide dramatic savings on installation labor, thus reducing costs
- ◆ Very tough diffusers resist breakage and reduce replacement and maintenance costs
- ◆ Available in 2', 4' & 8' lengths.
- ◆ Frosted lens for reducing direct glare and image of the LED
- ◆ Optional durable stainless steel mounting hardware
- ◆ No need to drill through the housing for installation
- ◆ Optional stainless steel bail for chain/cable hung installations
- ◆ ETL listed for wet location
- ◆ Consult for other options



### SPECIFICATIONS

High quality enclosed fiberglass fixture features a unique continuous poured gasket which completely fills channel for maximum seal integrity. Diffuser is held in place with POM retaining latches. Stainless steel latches are recommended for the following applications: agriculture, car washes, food processing and swimming pools. Hole is 7/8" diameter and is provided with a plastic plug on one end for conduit attachment. Offset mounting pads which keeps luminaire level and slightly off of mounting surface are formed within the housing. Standard diffuser is high impact acrylic with textured pattern designed for high efficiency while providing reduced glare. Listed by and bears ETL label.



### ORDERING DATA

EXAMPLE: VW2WDLED28DMVSF40

VW		LED		MV					
Series	Length	Distribution		Fixture	Wattage	Voltage	Lens	Kelvin Temperature	Accessories
VW	2'	Blank	Std.	LED	2 ft.	DMV 120-277	RF Ribbed Frosted	30	See
LED	4'				24			35	
Vaportight	8'	WD	Wide		4 ft.	0-10V Dimming	RC Ribbed Clear	40	Accessories Page
					48		SF Smooth Frosted	50	
					57		SC Smooth Clear		
					H72				
					8 ft.				
					97				
					114				
					H144				




Dimensions and specifications subject to change without notice.

◆ 800-444-WATT ◆ www.mobern.com ◆  
8200 Stayton Dr., Ste. 100, Jessup, MD 20794




CAT#	
JOB NAME	TYPE

**DIMENSIONS**

Side View



End View



**ACCESSORIES**

Clips and Hangers Accessories



- ◆ Replacement white latch
- ◆ 2 Ft. & 4 Ft. - H123



- ◆ Stainless steel latch kit
- ◆ 2 Ft. & 4 Ft - H126



- ◆ Stainless steel mounting bracket
- ◆ VWMB2L-2PK



- ◆ Stainless steel mounting bracket w/bail
- ◆ VWMB2L-B-2PK
- ◆ (Recommended for cable hanging)

Occupancy Sensor and Photo Cell Accessories

- OS
- PC120
- PC277

- Occupancy Sensor
- Photo Cell, 120V
- Photo Cell, 277V



Dimensions and specifications subject to change without notice.

◆ 800-444-WATT ◆ www.mobern.com ◆  
8200 Stayton Dr., Ste. 100, Jessup, MD 20794

CAT#	
JOB NAME	TYPE