



GE  
Lighting

### 35784 - Integrated 3ft LED Glass Tubes

#### LED11ET8/G/3/835

- ☞ Convert your existing linear fluorescent fixture to LED lighting without needing a comprehensive reinstall.
- ☞ Each LED tube is outfitted with an internal GE driver.
- ☞ The GE integrated LED tubes run on electronic T8 instant-start or programmed start ballasts.
- ☞ 66% longer life than LFL (50,000 vs. 30,000 hours)
- ☞ No UV
- ☞ Easy disposal, non-hazardous waste
- ☞ Check ballast compatibility at [www.gelighting.com/LEDTUBES-ballast-compatibility](http://www.gelighting.com/LEDTUBES-ballast-compatibility)
- ☞ UL Listed

#### Product Photo



#### GENERAL CHARACTERISTICS

Product Technology	LED
Rated Life (Hours)	50000 h
LED Tube Type	Glass
10 Digit U	4316835784
Lamp Count	1
Life in Years	45.7 yr
Replacement Watts	0 W
Requested Structure	Sleeve
Estimated Energy Cost per Year	1.39
Base	G13
Bulb Shape	T8

#### PHOTOMETRIC CHARACTERISTICS

Initial Lumens-nominal	1500 lm
Color Rendering Index-CRI	80
Color Temperature	3500 K

#### PRODUCT INFORMATION

Product Code	35784
Description	LED11ET8/G/3/835
Alternative Unit Of Measure	CASE
Standard Package Quantity	20
Ean UPC	043168357845
Standard Package GTIN	10043168357842
No Of Items Per Sales Unit	
No Of Items Per Standard Package	20
Sales Unit	Case
UCC	043168357845
Alternative Unit Of Measure	EACH
Standard Package Quantity	20
Ean UPC	043168357845
Standard Package GTIN	00043168357845
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	20
Sales Unit	Each
UCC	043168357845

#### DIMENSIONS

Bulb Max Overall Length-MOL	36.0 in
-----------------------------	---------

#### ELECTRICAL CHARACTERISTICS

Rated power (Watts)	11 W
---------------------	------