



84031-12: One Light Outdoor Wall Lantern



Dimensions:

Width: 8 1/2" **Extends:** 9 1/2"
Height: 15" **Wire:** 6 1/2"
Weight: 5 lbs. **Mounting Proc.:** Cap Nuts
Connection: Mounted To Box
Bulb Appearance: Clear

Bulbs:

1 - Medium A19 100w Max. 120v - Not included
 1 - LED Medium A19 8w Max. 120v - Not included
 1 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Clear bulb(s) recommended for this fixture
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Collection: Kent

One Light Outdoor Wall Lantern in Black Finish with Clear Beveled Glass.

Outdoor wall lantern finished black over die-cast aluminum with clear beveled glass.

Design #: D20033

UPC #:785652840319

Finish: Black (12)

Material List:

1 Body - Die Cast Aluminum - Black

Safety Listing:

Safety Listed for Wet Locations
 Safety Listed for Wet Locations

Instruction Sheets:

English (HC-408)
 French (F-009)
 Trilingual (English, Spanish, and French)
 (990W84029-84529-84031-84531-KEN)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Panel	Glass	Clear Beveled	4									
Panel	Glass	Clear Beveled	4									

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate			5/8	5 1/2	2 3/4	12 1/4

Replacement Bulb Data:

Product #		Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted	A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted	A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted	A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted	A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	84031-12	1	785652840319	11.25	10	17.75	1.156	6.2	150	Yes
NJ Pallet		56		48	40	69.75	77.5	297.6		No
NV Pallet		56		48	40	69.75	77.5	348		No