

LED-6000 Series T8 LED Retrofit

SKU (USA)

Description

| | |
|-----------------------|-----------------------------------------------------|
| LED-6115-UL-4-40K-BFR | 4' T8 LED, Frosted Lens, 4000K DLC |
| LED-6115-UL-4-57K-BFR | 4' T8 LED, Frosted Lens, 5700K |
| LED-6204-UL-4-40K-BFR | 4' T8 LED, Ballast Compatible, Frst Lens, 4000K DLC |
| LED-6123-UL-3-40K-BFR | 3' T8 LED, Frosted Lens, 4000K |
| LED-6111-UL-2-40K-BFR | 2' T8 LED, Frosted Lens, 4000K DLC |



Technical Specifications

| Models US/CAN | LED-6115-UL-4-40K-BFR | LED-6115-UL-4-57K-BFR | LED-6204-UL-4-40K-BFR | LED-6123-UL-3-40K-BFR | LED-6111-UL-2-40K-BFR |
|-------------------------------------------|-----------------------|-----------------------|-----------------------|-----------------------|-----------------------|
| CCT | 4000K | 5700K | 4000K | 4000K | 4000K |
| Power (Watts) | 18 | 18 | 18 | 15 | 10 |
| Replaces | T8 Fluorescent | | | | |
| Mounting | G13 | | | | |
| Instant Start ballast compatible | No | No | Yes | No | No |
| Direct Voltage Only (Must Bypass Ballast) | Yes | Yes | No | Yes | Yes |
| Voltage | 120-277VAC (USA) | | | | |
| Beam Angle | 120 | | | | |
| Dimmable | No | | | | |
| Operating Temp | 0°F - +90°F | | | | |
| Rated R70 Life | Up to 50,000 Hrs. | | | | |
| Warranty | 5 Year Limited* | | | | |
| LM79 Specifications | No | No | No | No | No |
| Power (W) | 18 | 18 | 18 | 15 | 10 |
| CCT | 4000 | 5700 | 4000 | 4000 | 4000 |
| Light Output | 1880 | 1880 | 1880 | 1350 | 1080 |
| Efficacy | 104 | 104 | 104 | 90 | 108 |
| THD @ 277V | TBA | TBA | TBA | TBA | TBA |
| PF @ 277V | TBA | TBA | TBA | TBA | TBA |
| CRI: | >80 | >80 | >80 | >80 | >80 |
| Packaging | 35 / Master Carton | | | | |
| Unit Dimension | 1.3" x 48.3" | | 1.3"x36.3 | 1.3"x24.3 | |
| Unit Weight | 1.3 lbs. | | 1.0 lbs | .75 lbs | |
| Master Dimension | 49.6" x 9.8" x 11" | | 37.6" x 9.8" x 11" | 25.6" x 9.8" x 11" | |
| Master Weight | 43.7 lbs. | | 36 lbs | 28 lbs | |

4' T8 LED

18W LED for PL
Replaces 32W T8



Features:

- 10-18w power consumption
- Replaces T8 Fluorescent
- >80 CRI
- 50,000 Rated L70 LED life
- 120-277V
- UL listed
- 5 Year warranty

Retrofit Models:

- Single End Power
- Must remove or bypass ballast
- G13 – Non-Shunted Sockets

Ballast Compatible (LED-6204):

- Works with Instant Start fluorescent ballasts only
- Double End Power - G13 Bi-Pin

Note: All specification information falls within a ± 2% range and is subject to change without notice.

NOTE: Light Efficient Design is providing this information to the general public. Please note that all products contained herein are trademarked, copyrighted, and/or have patents pending. Any use of these designs is strictly prohibited without prior written consent. Light Efficient Design protects its proprietary information vigorously in the courts of the United States of America.