



S9495

6.5MR16/LED/40'/27K/12V
 6.5 watt; LED MR16 LED; 2700K; 40' beam spread; GU5.3 base; 12 volt AC/DC

Features

- Silver back MR16 reflector
- Direct replacement for 50watt Halogen lamps
- Approved for enclosed fixtures
- Dimmable



S9495

Compatible Dimmers

- Leviton DSE06-10Z
- Lutron DVELV-300P
- Lutron DVLV-600P
- Lutron MAELV-600
- Lutron NTELV-300
- Lutron PD-5NE
- Lutron SELV-300P
- Lutron SLV-600P

Item Number	UPC	Voltage	Watts	Lamp Shape	Base	ANSI Base	Lamp Code		
S9495	045923094958	12v AC/DC	6.5	MR16	GU5.3	GU5.3	6.5MR16/LED/40'/27K/12V		
Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color		
Dimmable	Silver Back	1 3/4"	2"	500	25000	2700	Warm White		
CRI	Beam Spread Deg	Pack	ENERGY STAR	RoHS Compliant	UL or ETL Listed	UL Classification		Warranty	
80	40	12/48	ENERGY STAR	Yes	Yes	cULus - Damp Location Rated		3 Year Limited	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

