



GE
Lighting

43129 - Integrated U6 LED Plastic Tubes

LED13ET8/U6/840

- ☞ Convert your existing linear fluorescent fixture to LED lighting without needing a comprehensive reinstall.
- ☞ LED tubes are ideal for those seeking high energy savings with minimal installation time.
- ☞ Each LED tube is outfitted with an internal GE driver.
- ☞ GE integrated LED tubes run on electronic T8 instant-start or programmed start ballasts.
- ☞ Shatter resistant
- ☞ No UV
- ☞ Easy disposal, non-hazardous waste
- ☞ UL Listed

Product Photo



CAUTIONS & WARNINGS

Caution

Risk of Electric Shock

Suitable for damp locations

Not intended for use with emergency exit fixtures or emergency exit lights

GENERAL CHARACTERISTICS

Dimmable	Yes
Product Technology	LED
Rated Life (Hours)	50000 h
Dimmable / Non-Dimmable	Yes
LED Tube Type	Plastic
Lamp Count	1
Life in Years	45.7 yr
Replacement Watts	0 W
Requested Structure	Carton
Estimated Energy Cost per Year	1.57
Base	G13
Bulb Shape	T8-U6

PHOTOMETRIC CHARACTERISTICS

Initial Lumens-nominal	1900 lm
Color Rendering Index-CRI	80
Color Temperature	4000 K

PRODUCT INFORMATION

Product Code	43129
Description	LED13ET8/U6/840

DIMENSIONS

Bulb Max Overall Length-MOL	22.5 in
-----------------------------	---------

ELECTRICAL CHARACTERISTICS

Rated power (Watts)	13 W
---------------------	------