

111-00400

HellermannTyton



Article Number: 111-00400

Description: Heavy-Duty Cable Tie, 15.2" Long, UL Rated, 120lb Tensile Strength, PA66UV, Black, 100/pkg

Base Data	
Local Order Number	T120R0UVC2
Type	T120R
Color	Black (BK)
Features and benefits	<ul style="list-style-type: none"> • UV stabilized heavy duty cable ties contain an inhibitor which prolongs the life of the tie in UV exposures. • Head design provides high tensile strength with very low insertion force. • Bent tail ensures a quick and simple installation.
Quantity Per	bag
Product Description	HellermannTyton heavy duty cable ties offer a higher tensile strength for heavy load applications. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
Global Part Name	T120R-PA66UV-BK
Short Description	Heavy-Duty Cable Tie, 15.2" Long, UL Rated, 120lb Tensile Strength, PA66UV, Black, 100/pkg
Product Dimensions	
Minimum Tensile Strength (Imperial)	120.0lbs
Minimum Tensile Strength (Metric)	535.0N
Length L (Imperial)	15.2"
Length L (Metric)	387.0mm
Fixation Method	None
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.3"
Width W (Metric)	7.6mm
Bundle Diameter Min. (Imperial)	0.2"

111-00400



Product Dimensions	Bundle Diameter Min. (Metric)	5.0mm
	Bundle Diameter Max. (Imperial)	4.1"
	Bundle Diameter Max. (Metric)	105.0mm
	Thickness T (Imperial)	0.07"
	Thickness T (Metric)	1.8mm
Material and Specifications		
	Material	Polyamide 6.6 UV-resistant (PA66UV)
	Material Shortcut	PA66UV
	US MILSPEC	MS3367-3-0
	Flammability	UL 94 V2
	Halogenfree	Yes
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
	Certification/Specification WEB	BACS38K, CAGE Code 53421, UL-ZODZ2.E64139
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100Pieces
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces
	Weight (Metric)	5.14kg