

CFL LAMP

SPECIFICATIONS

Ideal For

General Purpose

Soft White
2700K

Features

- FCC Compliant
- RoHS Compliant
- 2 Year Warranty
- Soft White
- Contains Post Consumer Recycled Material

Benefits

- Energy Efficient: Up to 78% less energy than standard incandescent
- Low Heat
- Durable
- Long Life



Specifications

Item Number	Input Power (Watts)	Incandescent Equiv. (Watts)	Input Line Voltage
ESL13T/ECO	13	60	120
Base Type	Lumens	Lumen Efficiency (LPW)	CCT
E26 (Medium)	900	69	2700K
MOL	Diameter	Life Hours	
4.3"	1.86"	10,000	