

# L.I.P.<sup>™</sup> CONDUIT SHEAVES

LOCK-IN-PLACE FEEDING SHEAVES

**iTOOLco.**



Locks in place - overhead at any angle - in under a minute



Fully adjustable thread depth

L.I.P.<sup>™</sup> (Lock-in-Place) Conduit Feeding Sheaves lock in place at any angle or inclination. The phenolic resin wheel is more durable than cast and won't dent or break. Unlike conventional sheaves, L.I.P.<sup>™</sup> Conduit Sheaves enable the installer to stay clear of the equipment, keeping hands and limbs safety out of the way. Needle bearing rollers ensure a smooth installation by minimizing drag on the pull and reducing the risk of damaging valuable wire.



Reduces risk of damaging valuable wire

Watch Video




**FASTER SAFER WORKSPACE**

# L.I.P.™ CONDUIT SHEAVE

**iTOOLco.**

THE INDUSTRY'S FIRST DESIGN & FUNCTION IMPROVEMENT EVER



Model	Description	Specifications
<b>CS20</b>	2" Lock-in-Place Sheave	15"L x 6"W x 5"H, 6 lb.
<b>CS25</b>	2.5" Lock-in-Place Sheave	15"L x 6"W x 5"H, 7 lb.
<b>CS30</b>	3" Lock-in-Place Sheave	16"L x 7"W x 6"H, 12 lb.
<b>CS35</b>	3.5" Lock-in-Place Sheave	16"L x 7"W x 6"H, 12 lb.
<b>CS40</b>	4" Lock-in-Place Sheave	16"L x 7"W x 6"H, 12 lb.
<b>CS24 SET</b>	2" - 4" Lock-In-Place Sheave kit	(5 Sheaves)
Standard Sheaves		
<b>CS50</b>	5" Standard Sheave	16"L x 7"W x 7"H, 13 lb.
<b>CS60</b>	6" Standard Sheave	17"L x 8"W x 8"H, 13 lb.
<b>CS56 SET</b>	5" - 6" Standard Sheave kit	(2 Sheaves)

**6**  
YEAR  
LIMITED  
WARRANTY

MADE IN THE  
**USA**  
WITH GLOBAL  
COMPONENTS

Patent Pending