



S9623

9.5BR30/LED/5000K/750L/120V/D
9.5 watt; BR30 LED; 105' beam spread; 5000K; Medium base;
120 volts; Dimmable

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable



S9623

Item Number	Product Line	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape
S9623	DiTTO	045923096235	120	9.5	65W	0.91	BR30

Base	ANSI Base	Lamp Code	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches	Initial Lumens
Medium	E26	9.5BR30/LED/5000K/750L/120V/D	Compatible dimmers for S9623	Frosted	5-3/16"	3-3/4"	750

Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR
25000	5000	Natural Light	80	105	12/6	Box	ENERGY STAR

RoHS Compliant	UL or ETL Listed	UL Classification	Warranty
Yes	Yes	cULus - Damp Location Rated	3 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

