

# T3030K0044B

by Acme Electric

Catalog ID: T3030K0044B



\* Reverse Voltage Distribution Transformer - Three Phase, 240Δ - 208Y/120V, 30kVA

- Quiet operation with sound levels below NEMA standards

## Product Details

---

### General

ANFC Taps	2
-----------	---

BNFC Taps	2
Construction	Ventilated
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	240Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	208Y/120 V
Taps % Steps	2.5%
UL Insulation Class	220°C
Winding Material	AL
kVA	30

## Dimensions

Height	25.5 in
Length	19.37 in
Weight	325 lb
Width	24.39 in

## Electrical Ratings

Efficiency	98.23%
Frequency Rating	60 Hz

Primary Voltage	240D V
-----------------	--------

Certifications and Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 3R
UL Standard	UL 1561