



*Hoffman*

## Screw-Cover, Type 3R

Catalog Number: A12R128NK  
US List Price (USD): \$83.56

### Bulletin Number:

- A90S3

### Material:

- Steel



### Model Code:

- 13513

### Ship Wt. Std. Pkg. (lbs):

- 14.56

### Interchangeable:

- False

### Finish:

- Galv/paint

### Industry Standards:

UL 50, 50E Listed; Type 3R; File No. E27525 cUL Listed per CSA C22.2 No 94; Type 3R; File No. E27525 NEMA/EEMAC Type 3R IEC 60529, IP32

## Description

Use this enclosure with or without knockouts in outdoor applications as a wiring or junction box.

### Description:

- Drip shield top and seam-free sides, front and back
- Slip-on removable cover fastened with plated steel screws along bottom edge
- Handles on larger sizes (see table)
- Embossed mounting holes on back of enclosure
- Knockouts in bottom of 16 and 14 gauge enclosures
- Provision for padlocking
- No gasketing
- See also Accessories.
- Industrial Corrosion Inhibitors
- Electric Heater Grounding Device
- Mounting Bracket Kit
- Touch-Up Paint
- ANSI 61 gray polyester powder paint finish inside and out over pretreated surfaces.
- 16, 14 or 12 gauge galvanized steel
- Use this enclosure with or without knockouts in outdoor applications as a wiring or junction box.

## Technical Data

---

### Screw-Cover, Type 3R

<b>Catalog Number</b>	<a href="#">A12R128NK</a>
<b>A in.</b>	12
<b>B in.</b>	12
<b>C in.</b>	8
<b>D in.</b>	—
<b>Mounting H in.</b>	2.25
<b>Body Style</b>	A
<b>Mounting J in.</b>	1.06

## Certifications

---



EU Certification



UL Certification

## Documents

---



3D STEP CAD



2D DXF CAD



Spec Sheet



Dimension Drawing

No accessories available.