

MINKA-LAVERY®

Item #: 3382-77	UPC Code: 747396098265
Product Family Name: D'or	Finish: Chrome
Category: Bath	Category Type: Bath
Certification 3057374	
Patents	
Notes:	



Image File Name:
3382-77--
1475636406.jpg



MEASUREMENTS

Width: 15	Length: 7.75	Height: 7.75	Extension: 7.75
Height Adjustable: No	Min Overall Height:	Max Overall Height:	Slope: No
Wire Length: 7	Chain Length:	Safety Cable Included: No	Net Weight: 6.92
Canopy Width: 8.50	Canopy Height: 4.75	Canopy Length:	
Backplate Width:	Backplate Height:	Center to Top: 3.75	Center to Bottom: 4.00

LAMPING

No. of Bulbs: 2	Light Type: A-19,Medium			
Max Bulb Wattage: 100	Socket: E26,Medium			
Dimmable: Yes	Ballast:	Rated Life Hours:	Photocell Included: N	Lamps Included: No
Lamp Included: No	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:

SHADE / GLASS

Description:	Material: Glass
Part No.: G3381	Quantity: 2
Width: 5.25	Height: 5.75
	Length: 5.25



SHIPPING

Carton Width: 10.250	Carton Height: 12.000	Carton Length: 17.250
Carton Weight: 9.200	Carton Cubic Feet: 1.228	Small Package Shippable: Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		Master Pack: 1



Damp
Location
Yes



ETL Intertek
Yes