



Candle/Decorative LED

4.5B11/LED/827/E12/CL/DIM 1PK 10/1

Philips Candle Dimmable LED Lamps offer decorative energy saving ambience with the elegant effect of incandescent candles. Available in bent, blunt and flame tip candles, their unique design provides light in all directions, giving lighting designers a long life alternative to standard incandescent sources.

Product data


General Information		Starting Time (Nom)	
Cap-Base	E12 [Candelabra Screw]	Starting Time (Nom)	0.5 s
Nominal Lifetime (Nom)	15000 h	Warm Up Time To 60% Light (Nom)	0.5 s
Switching Cycle	50000X	Power Factor (Nom)	0.7
Technical Type	4.5-40W	Voltage (Nom)	120 V
Light Technical		Temperature	
Color Code	827 [CCT of 2700K]	T-Case Maximum (Nom)	80 °C
Initial lumen (Nom)	300 lm	Controls and Dimming	
Luminous Flux (Rated) (Nom)	300 lm	Dimmable	Yes
Color Designation	Warm White (WW)	Mechanical and Housing	
Correlated Color Temperature (Nom)	2700 K	Bulb Finish	Clear (CL)
Luminous Efficacy (rated) (Nom)	66.7 lm/W	Approval and Application	
Color Consistency	ANSI 2700K	Energy star mark	Energy star
Color Rendering Index (Nom)	80	Suitable For Accent Lighting	No
LLMF At End Of Nominal Lifetime (Nom)	70 %	Product Data	
Operating and Electrical		Order product name	4.5B11/LED/827/E12/DIM 120V
Input Frequency	60 Hz	EAN/UPC - Product	046677461874
Power (Rated) (Nom)	4.5 W	Order code	461871
Lamp Current (Nom)	43 mA		
Wattage Equivalent	40 W		

Candle/Decorative LED

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001213704

Net Weight (Piece)	0.040 kg
--------------------	----------



Dimensional drawing



Candle B11 300lm 2700K E12 D CL

Product	C	D
4.5B11/LED/827/E12/DIM 120V	105 mm	36 mm

Photometric data



CalcLuX Photometrics 4.3

Philips Lighting B.V.

Page 1/1

