


U214MTB-P



4 Terminal Ring Type Small Closing Plate Link Bypass 1-100
Ampere Main Pullout

SPECIFICATIONS

Brand Name	Milbank
Type	Ring Type Meter Socket
Application	Meter Socket With Main
Standard	UL Listed;Type 3R
Voltage Rating	Up to 240 Volts Alternating Current
Amperage Rating	100 Continuous Ampere
Phase	1 Phase
Frequency Rating	60 Hertz
Size	4.625L x 18.125W x24.75H
Number of Main Breakers	1
Main Breaker Size	One 100 Ampere Main Fuse Pull Out Switch
Cable Entry	Overhead or Underground
Terminal	Single Mechanical



Insulation	Fiberglass with Resin
Mounting	Surface Mount
Material	G90 Galvanized Steel with Powder Coat Finish
Number of Jaws	6 Terminal
Bypass Provision	Link Bypass
Number of Meter Positions	1 Position
Equipment Ground	Ground Lug
Hub/Closing Plate	Twin Small Closing Plates
Line Side Wire Range	14 AWG - 1/0
Load Side Wire Range	14 - 1/0 AWG
Number of Receptacles	0
Height	24.75 IN
Length	4.625 IN
Width	18.125 IN

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility, and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.

