



Hoffman

Horizontal-Mount, Type 3R

Catalog Number: A24R206HM
US List Price (USD): \$155.90

Bulletin Number:

- A90RH

Material:

- Steel



Model Code:

- 15357

Ship Wt. Std. Pkg. (lbs):

- 37.0

Interchangeable:

- False

Industry Standards:

Maintains Type 3R rating when mounted horizontally. Maintains Type 1 rating when mounted vertically. UL 50, 50E Listed; Type 3R; File No. E27525 cUL Listed per CSA C22.2 No 94; Type 3R; File No. E27525 NEMA/EEMAC Type 3R IEC 60529, IP32

Description

Use this enclosure as a wiring, junction or pull box for outside horizontal mounting applications such as rooftops or pads. Vertical structure for mounting is not required.

Applications:

Use this enclosure as a wiring, junction or pull box for outside horizontal mounting applications such as rooftops or pads. Vertical structure for mounting is not required.

Features:

- The screw cover is the drip shield providing 3/4-in. overhang on each side for outdoor protection
- No gasketing
- Screw locations on cover are embossed
- Enclosure body flange is formed outward
- Mounting holes on back for direct mounting through the back to strut or mounting surface; vertical structure for mounting not required
- Optional mounting brackets (included) provide a 1-in. clearance off surface for protection against pooling water

Specifications:

16 or 12 gauge galvanized steel

Finish:

ANSI 61 gray polyester powder paint finish inside and out over pretreated surfaces.

Accessories:

Touch-Up Paint

Technical Data

Horizontal-Mount, Type 3R

Catalog Number [A24R206HM](#)

A in.	24
B in.	20
C in.	6
L in.	25.83
G in.	21.50
H in.	17.50
W in.	20.38

Certifications



EU Certification



UL Certification

Documents



Spec Sheet



Instruction Manual



Dimension Drawing

No accessories available.