

111-04878

# HellermannTyton



Article Number: 111-04878

Description: Standard Cable Tie, 8" Long, UL Rated, 50lb Tensile Strength, PA66, Black, 100/pkg

Base Data	
Local Order Number	T50R0C2
Type	T50R
Color	Black (BK)
Features and benefits	<ul style="list-style-type: none"> <li>• Engineered and manufactured for maximum performance and quality.</li> <li>• Made from 100% high-quality plastic to ensure efficient recycling.</li> <li>• Inside serration for a strong hold onto bundles.</li> <li>• Easy application either manually or with a processing tool.</li> <li>• Bent tail allows for simpler insertion.</li> </ul>
Quantity Per	bag
Product Description	T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.
Global Part Name	T50R-PA66-BK
Short Description	Standard Cable Tie, 8" Long, UL Rated, 50lb Tensile Strength, PA66, Black, 100/pkg
Product Dimensions	
Minimum Tensile Strength (Imperial)	50.0lbs
Minimum Tensile Strength (Metric)	225.0N
Length L (Imperial)	8.0"
Length L (Metric)	202.0mm
Fixation Method	None
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.18"
Width W (Metric)	4.6mm
Bundle Diameter Min. (Imperial)	0.06"

111-04878



Product Dimensions	Bundle Diameter Min. (Metric)	1.5mm
	Bundle Diameter Max. (Imperial)	1.97"
	Bundle Diameter Max. (Metric)	50.0mm
	Thickness T (Metric)	1.2mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	US MILSPEC	MIL 53421
	Flammability	UL 94 V2
	Halogenfree	Yes
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	ROHS Compliant	Yes
	UL Listed (US and Canada)	Yes
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100
	Customs Number(Schedule B)	3926909987