



# S9752

60W/LED/HID/MB/5000K/100-277V  
 60 watt - LED HID Replacement; 5000K; Mogul extended base;  
 100-277 volts

### Features

- Replaces HID, CFL, and Incandescent
- Direct wire range voltage 100-277V
- Approved for totally enclosed fixtures
- Hi bay, low bay and post top
- Light panels lock into place creating 3 separate beam angle options
- IP65 rated
- DLC Qualified
- 5 year limited warranty

Specification note: Power Factor >0.9; Operating temperature range -20°C to 65°C; Operating Frequency 50-60Hz; Working Voltage AC 90-305V

Optional accessory: In-line surge protector [80-929](#)



S9752

Width (360°)	Width (270°)	Width (180°)
3.8"	8.2"	9.3"

Minimum lamp compartment dimensions: 235mm x 235mm x 210mm ( 9.25" x 9.25" x 8.27" )

Item Number	Product Line	UPC	Input Voltage	Watts	Incandescent Equivalent	Fluorescent Equivalent	HID Equivalent	
S9752	Hi-Pro	045923097522	100 - 277	60	500W	85W	250W	
Power Factor	Base	ANSI Base	Lamp Code		Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches
0.90	Mogul Extended	EX39	60W/LED/HID/MB/5000K/100-277V		Non-Dimmable	White	8-9/16"	3-13/16" (Open 9-5/16")
Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature		Pack
7800	50000	5000	Natural Light	80+	Adjustable: 360; 270; 180	-20C (-4F) to a maximum of +65C (+149F)		12/6
Package Type	DLC ID:	RoHS Compliant	Fixture Type	UL or ETL Listed	UL Classification	Warranty		
Box	PZY8T15P <a href="#">DLC Search</a>	Yes	Enclosed Rated	Yes	cULus - Damp Location Rated	<a href="#">5 Year Limited</a>		