

Item # 72541-593	UPC Code:
Product Family Name: Astrapia II	Finish: Dark Rubbed Sienna
Category:	Category Type:
Certification:	
Patents:	
Notes:	



Image File Name: 72541-593.jpg



MEASUREMENTS

Width: 7	Length: 0.00	Height: 19.75	Extension: 8.75
Height Adjustable: No	Min Overall Height: 0.00	Max Overall Height: 0.00	Slope: No
Wire Length: 7"	Chain Length:	Safety Cable Included: No	Net Weight: 5.38
Canopy Width: 0.00	Canopy Height: 0.00	Canopy Length: 0.00	Center to Bottom: 9.50
Backplate Width: 0.00	Backplate Height: 0.00	Center to Top: 10.13	

LAMPING

No. of Bulbs: 2	Light Type: B10,Cand			
Max Bulb Wattage: 60	Socket: E12, Candelabra			
Dimmable: Yes	Ballast:	Rated Life Hours:	Photocell Included: No	Bulb/LED Included:
Bulb/LED Included:	Color Temp.: 0	CRI:	Initial Lumens:	Delivered Lumens:

SHADE / GLASS

Description:	Material:
Part No.:	Quantity: 4
Width: 3.75	Height: 7.25
	Length: 4.75



SHIPPING

Carton Width: 10.25	Carton Height: 22.75	Carton Length: 11.75
Carton Weight: 7.46	Carton Cubic Feet: 1.59	Small Package Shippable: Yes
Master Pack Width: 0.00	Master Pack Height: 0.00	Master Pack Length: 0.00
Master Pack Weight: 0.00	Master Cubic Feet: 0.00	Multi-Pack: 0
		Master Pack: 1