



## 8038-12: One Light Outdoor Wall Lantern



### Dimensions:

<b>Width:</b>	7 3/4"	<b>Extends:</b>	7 1/2"
<b>Height:</b>	12"	<b>Wire:</b>	6 1/2"
<b>Weight:</b>	4 lbs.	<b>Mounting Proc.:</b>	Cap Nuts
		<b>Connection:</b>	Mounted To Box
		<b>Bulb Appearance:</b>	Clear

### Bulbs:

- 1 - Medium A19 100w Max. 120v - Not included
- 1 - LED Medium A19 8w Max. 120v - Not included
- 1 - LED Medium A19 13.5w Max. 120v - Not included

### Features:

- Clear bulb(s) recommended for this fixture
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

**Collection:** Lancaster

Medium Solid Brass Classic One Light Wall Lantern in Black Finish and Clear Curved Beveled Glass.

Medium solid Brass Classic One Light outdoor Wall Lantern in Black Finish and Clear Beveled Glass.

**UPC #:**785652803802

**Finish:** Black (12)

### Material List:

- 1 Body - Brass - Black

### Safety Listing:

- Safety Listed for Wet Locations
- Safety Listed for Wet Locations

### Instruction Sheets:

- English (HC-231)
- French (F-009)

### Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Panel	Glass	Clear Curved Beveled	6									

### Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	5 9/16	4 11/16	5/8		4 1/2	7 1/2

### Replacement Bulb Data:

Product #		Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted	A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted	A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted	A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted	A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	8038-12	1	785652803802	10.5	10.75	14	0.914	5.1	150	Yes
NJ Pallet		70		48	40	70.25	78.056	657		No

NV Pallet		70		48	40	70.25	78.056	657		No
-----------	--	----	--	----	----	-------	--------	-----	--	----