



8038-71: One Light Outdoor Wall Lantern



Dimensions:

Width: 7 3/4" **Extends:** 7 1/2"
Height: 12" **Wire:** 6 1/2"
Weight: 4 lbs. **Mounting Proc.:** Cap Nuts
Connection: Mounted To Box
Bulb Appearance: Clear

Bulbs:

1 - Medium A19 100w Max. 120v - Not included

Features:

- Clear bulb(s) recommended for this fixture
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Material List:

1 Body - Brass - Antique Bronze

Safety Listing:

Safety Listed for Wet Locations
 Safety Listed for Wet Locations

Instruction Sheets:

English (HC-231)
 French (F-009)

Collection: Lancaster

Medium Solid Brass Classic One Light Wall Lantern in Antique Bronze Finish and Clear Curved Beveled Glass.

Medium solid Brass Classic One Light Outdoor Wall Lantern in Bronze Finish and Clear Beveled Glass.

UPC #:785652803819

Finish: Antique Bronze (71)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Panel	Glass	Clear Curved Beveled	6									

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	5 9/16	4 11/16	5/8		4 1/2	7 1/2

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	8038-71	1	785652803819	10.75	10	15	0.933	4.95	175	Yes
NJ Pallet		70		48	40	69.8	77.556	346.5		No
NV Pallet		70		48	40	69.8	77.556	346.5		No