



# S9499

6.5MR16/LED/40'/50K/12V  
 6.5 watt; LED MR16 LED; 5000K; 40' beam spread; GU5.3 base; 12 volt AC/DC

### Features

- Silver back MR16 reflector
- Direct replacement for 50watt Halogen lamps
- Approved for enclosed fixtures
- Dimmable



S9499

Item Number	UPC	Voltage	Watts	Power Factor	Lamp Shape	Base	ANSI Base
S9499	045923094996	12v AC/DC	6.5	0.96	MR16	GU5.3	GU5.3
Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
6.5MR16/LED/40'/50K/12V	Dimmable	<a href="#">Compatible dimmers for S9499</a>	Silver Back	1 3/4"	2"	500	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	ENERGY STAR	CEC Status
5000	Natural Light	80	40	-25C (-13F) to a maximum of +45C (+113F)	12/48	ENERGY STAR	Lawful for sale in California
RoHS Compliant		UL or ETL Listed		Warranty			
Yes		Yes		<a href="#">5 Year Limited - 10 hour use per day</a>			