



88240-780: One Light Outdoor Wall Lantern



Collection: Cape May

One Light Wall Lantern in Burled Iron Finish with Etched Hammered with Light Amber Glass Shade

UPC #:785652882401

Finish: Burled Iron (780)

Dimensions:

Width:	7"	Extends:	8"
Height:	10 1/2"	Wire:	6 1/2"
Weight:	2.7 lbs.	Mounting Proc.:	Cap Nuts
		Connection:	Mounted To Box

Bulbs:

- 1 - Medium A19 100w Max. 120v - Not included
- 1 - LED Medium A19 8w Max. 120v - Not included
- 1 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Material List:

1 Body - Aluminum - Burled Iron

Safety Listing:

Safety Listed for Wet Locations
Safety Listed for Wet Locations

Instruction Sheets:

English (HC-1178)
French (F-009)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Diffuser	Glass	Etched Hammered with Light Amber	1				5 15/16	5 11/32				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	7 1/16	4 1/2	1		3	7 3/8

Replacement Bulb Data:

Product #		Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted	A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted	A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted	A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted	A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	88240-780	1	785652882401	13.5	10.5	9.75	0.8	3.4	150	Yes
NJ Pallet		84		48	40	75	83.333	285.6		No
NV Pallet		84		48	40	71.25	79.167	285		No