



Mogul Extended	EX39	100W/LED/HID/4000K/100-277V/EX39			Non-Dimmable	White	9-5/8"	5.87"	13000
Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature		Pack	Package Type	
50000	4000	Cool White	80+	300	-20C (-4F) to a maximum of +65C (+149F)		4	Box	
DLC ID:		RoHS Compliant	UL or ETL Listed	UL Classification	Warranty				
Search under: S9676A or PFNR9J3E or PM8Q4J33 <a href="#">DLC Search</a>		Yes	Yes	cULus - Damp Location Rated	<a href="#">5 Year Limited</a>				



<p>National Toll-Free: 800.43.SATCO (800.437.2826) <a href="http://www.satco.com">www.satco.com</a></p>	<p>Distribution Centers: New York, Florida, Texas, Washington, California, Puerto Rico</p>	<p>Corporate Offices: 110 Heartland Blvd., Brentwood, NY 11717 800.437.2826 631.243.2022 Fax 631.243.2027</p>	
---	--	---	---