

**Ferron Collection**  
**60 Inch Ferron Ceiling Fan OBB**  
 300160OBB (Oil Brushed Bronze)

Project Name: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Qty: \_\_\_\_\_  
 Comments: \_\_\_\_\_



**Product Information**

Product ID	300160OBB
Finish	Oil Brushed Bronze
Blade Finish	Oil Brsh Bronze/Non-Reversible
Collection	Ferron Collection

**Specifications**

Number of Blades	2
Blades Included	Yes
Blade Pitch	14 Degrees
Blade Sweep	60"
Blades Reversible	No
Blade Material	POLYCARBONATE
Optional Blades Available	No
Downrod 1	1.00 OD X 6.00
Primary Control System	6 Speed Dc Cooltouch
Remote Included	Yes
Wall Control Included	No
Low Ceiling Adaptable	No
Lead Wire Length	78.00"
Motor Size	125
Motor Type	DC

**Dimensions**



Downrod	A	B	C	D
1.00 OD X 6.00	15.92	15.37	7.25	5.90

**Downlight**

Downlight Bulb Included	Not Included
Watts	32/5
Glass Description	N/A
Optional Light Kit Available	No

**Safety Listings & Certifications**

Safety Rated	Dry
Warranty	<a href="http://www.kichler.com/warranty">www.kichler.com/warranty</a>

**Installation**

The electrical junction box and support structure must be securely mounted and capable of reliably supporting a minimum of 50 pounds. Use only ETL/UL listed electrical junction boxes

**Ferron Collection**  
**60 Inch Ferron Ceiling Fan OBB**  
 300160OBB (Oil Brushed Bronze)

Project Name: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Qty: \_\_\_\_\_  
 Comments: \_\_\_\_\_

**Available Finishes**

Finish	Fixture	Glass	Blade 1	Blade 2
Oil Brushed Bronze	300160OBB	N/A	OIL BRS BRONZE	NON-REVERSIBLE
Polished Nickel	300160PN	N/A	CHAMPAGNE	NON-REVERSIBLE

	marked ""For Fan Support""
Electrical Requirements	120V 60Hz AC
Hanging Weight	16.7 LBS
Minimum Distance Between Bottom Of Fan Blade To Floor	7.5 feet