

FLEXIBLE AND PORTABLE CORD

Type SOOW
EPDM Insulation -CPE Jacket
90C -600 Volt
2-6 AWG



CONSTRUCTION	
Conductor	- Fully annealed stranded bare copper
Insulation	- Ethylene Propylene Diene Monomer (EPDM)
Jacket	- Chlorinated Polyethylene (CPE)

Applications:

- Portable tools and equipment
- Portable appliances
- Small motors and associated machinery

Standards:

- MSHA Approved

COLOR CODE CHART	
Cond. #	Color
1	Black
2	White
3	Green
4	Red
5	Orange

Part #	AWG	Conductors	Insulation Thickness	Nom. O.D.	Lbs./M'
B10603	6	3	.050"	.790"	482
B10604	6	4	.050"	.865"	599
B10605	6	5	.050"	.945"	750
B10402	4	2	.050"	.890"	500
B10403	4	3	.050"	.925"	683
B10404	4	4	.050"	1.015"	851
B10405	4	5	.050"	1.115"	1039
B10203	2	3	.055"	1.085"	1003
B10204	2	4	.055"	1.17"	1248
B10205	2	5	.055"	1.39"	1684

*Fittings are available for these products.

Note: The information in this specification sheet is approximate and subject to standard industry and manufacturer tolerances. Please verify specific requirements with your Omni Cable account manager.

*UL and CSA material available

*Green conductor available for grounding only