

E12LED104

2.5W LED Candle Filament

DESCRIPTION

Perfect for lanterns or any exposed bulb application
Classic filament design creates a unique vintage feel in any room
15,000 hours lifespan is guaranteed.
EMC Compliant

PERFORMANCE

- Compatible with most dimmers;
- Dimming smoothly from 10% to 100%.
- 25W Incandescent replacement;
- UL compliant, FCC certified, Energy star qualified

CONSTRUCTION

- Glass cover
- Filament
- Integrated driver
- Cuprum E12 base

INSTALLATION

- Directly replace a25W incandescent lamp.
- Suitable for damp locations; indoor use only
- 120V AC input

PHOTOMETRIC

Model#	E12LED104
Luminous flux	165LM
Input wattage	2.5W
Lumens per watt	66LM/W
Beam angle	300°

Elitco Lighting



LED Filament

E12LED104

Specifications

Model #	E12LED104
Input Voltage	120V AC
Color Temperature	2700K
CRI	>80
Current	23mA
Watts	2.5W
Watt Equivalent	25W
Lumens	66LM/W
Beam Angle	300°
Dimmable	Yes
Lens	N/A
Rating	FCC, UL, ES
Dimensions	1.38*4.11"
Power Factor	0.9
Mounting	Connect to city power directly
LED Type	EPISTAR
Average Life (Hrs)	15,000 hrs.
Warranty	2 Years Limited