

ST18LED301

3W LED FILAMENT ST18 BULB E26

DESCRIPTION

This lamp is specifically for indoor lighting, 15,000 hours lifespan is guaranteed.

It will not interfere other electrical devices such as electronic garage controller.

PERFORMANCE

- Suitable for indoor lighting.
- Dimmable with most dimmer;
Dimming smoothly from 5% to 100%.
- 40W ST18 halogen replacement;
compared to halogen lamps with a rated life of 15,000 hours;
- ETL compliant, FCC certified.

CONSTRUCTION

- Amber Glass housing
- Electroplated Base
- Integrated driver


INSTALLATION

- Directly replace a 40W ST18 halogen lamp.
- Suitable for dry locations.
- 120V,60Hz input.

PHOTOMETRIC

Model#	ST18LED301
Luminous flux	300LM
Input wattage	3W
Lumens per watt	100LM/W
Beam angle	360°

Elitco Lighting



LED LIGHT BULB

ST18LED301



Specifications

Model #	ST18LED301
Input Voltage	120V,60Hz
Color Temperature	2200K
CRI	>80
Current	30mA
Watts	3W
Watt Equivalent	40W
Lumens	100LM/W
Beam Angle	360°
Dimmable	Yes
Housing Material	Glass
Lens	N/A
Rating	FCC, ETL
Dimensions	2.52*5.51"
Power Factor	0.9
Mounting	Plug-in
LED Type	Epistar
Average Life (Hrs)	15,000 hrs.
Warranty	2 Years Limited