

**OVERVIEW**

The Fresco Power Supply (FCS PS10) is a Class 2 low voltage power supply intended to power a single Fresco Touchscreen, or other 24VDC Acuity Controls devices. The FCS PS10 is intended for use with 120-277V, 50/60Hz circuits.

**FEATURES**

- Provided with Fresco touchscreens
- Available separately for use as low voltage power supply for Acuity Controls equipment
- 24VDC output, Class 2 Circuit
- 120-277V, 50/60Hz input
- Supplies 10W@ 40°C, 7W@50°C
- Consumes 12W@120V, 14W@277V
- UL Listed (E110912)
- Suitable for Plenum Use (UL2403)

**ENVIRONMENTAL**

- Maximum Ambient : 122°F/50°C
- Minimum Ambient : 32°F/0°C
- Relative Humidity: 90% non-condensing
- Designed for permanent interior installation

**Warranty**


Two-year limited warranty. Complete warranty terms located at: [www.acuitybrands.com/CustomerResources/Terms\\_and\\_conditions.aspx](http://www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx)

**Note:** Actual performance may differ as a result of end-user environment and application.


Specifications subject to change without notice.



**FCS PS10 Power Supply**  
Low Voltage Power Supply



**DIMENSIONS (inches/mm)**




**ORDERING INFORMATION**


Example: FCS PS10		
Series	Model	
FCS Fresco Control System	PS10 10W Power Supply	

# INSTALLATION

## ONE JUNCTION BOX



## TWO JUNCTION BOXES



## WIRING CONNECTIONS

