



S9812

11.5A19/LED/4000K/1100L/120V/D
11.5 watt; A19 LED; 4000K; Medium base; 220° beam spread;
120 volts

Features

- A-Shaped replacement lamp
- 75w equivalent
- 220° beam angle
- UL approved for totally enclosed fixtures
- Damp location rated
- Dimmable



S9812

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S9812	045923098123	120	11.5	75W	0.92	A19	Medium

ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches	Initial Lumens
E26	11.5A19/LED/4000K/1100L/120V/D	Dimmable	Compatible dimmers for S9812	Frosted	4-5/8"	2-3/8"	1100

Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type
25000	4000	Cool White	80	220	-20C (-4F) to a maximum of +45C (+113F)	24/6	Box

ENERGY STAR	RoHS Compliant	UL or ETL Listed	UL Classification	Warranty
ENERGY STAR	Yes	Yes	Damp	3 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

