




Full Product Options Shown on Reverse Side

GB SERIES INDUSTRIAL SPECIFICATION GRADE Set Screw, Threaded and Threadless Insulated Grounding Bushings With and Without Optional Ground Lug

Furnished with 3 Pre-Drilled Holes and Set Screws,
Unique Design Allows Ease of Installation and Orientation of Set Screw & Ground Lugs

Solid Steel or Aluminum Body with Hex Nut Design Permits Industrial Grade Torque without Damage to Pipe
Solid Machined Steel Zinc Plated or Galvanized Plated Product
Superior Life & Performance Over Zinc Die Cast Products
Furnished with UL Component Temperature Rated 150°C Insulated Throat
Available with Aluminum (Standard) Ground Lug or Copper



Galvanized Plating Available
Mechanically Galvanized Plating Equivalent To ASTM A-153
Hot-dip Performance Criteria in Harsh Environments such as Below Grade Work
Superior Plated Product, Will Not Flake Off When Installed

| GB Product Series WITH Grounding Lugs | | | | | GB Product Series WITHOUT Grounding Lug | | | |
|---------------------------------------|------------|-------------------------|-----------------------|----------------------|-----------------------------------------|------------|-------------------------|-----------------------|
| Product Series | TRADE SIZE | A Outside Diameter " | B Overall Length " | C Length of Lug " | Product Series | TRADE SIZE | A Outside Diameter " | B Overall Length " |
| GB 50BGL | 1/2" | 1.06 | .63 | .75 | GB 50B | 1/2" | 1.06 | .63 |
| GB 75BGL | 3/4" | 1.22 | .63 | .75 | GB 75B | 3/4" | 1.22 | .63 |
| GB 100BGL | 1" | 1.50 | .75 | .75 | GB100B | 1" | 1.50 | .75 |
| GB 125BGL | 1-1/4" | 1.88 | .78 | .75 | GB125B | 1-1/4" | 1.88 | .78 |
| GB 150BGL | 1-1/2" | 2.16 | .78 | .75 | GB150B | 1-1/2" | 2.16 | .78 |
| GB 200BGL | 2" | 2.16 | .78 | .75 | GB200B | 2" | 2.16 | .78 |
| GB 250BGL** | 2-1/2" | 3.21 | 1.05 | 1.10 | GB250B ** | 2-1/2" | 3.21 | 1.05 |
| GB 300BGL** | 3" | 3.96 | 1.08 | 1.10 | GB300B ** | 3" | 3.96 | 1.08 |
| GB 350BGL** | 3-1/2" | 4.47 | 1.08 | 1.10 | GB350B ** | 3-1/2" | 4.47 | 1.08 |
| GB 400BGL** | 4" | 5.15 | 1.18 | 1.70 | GB400B ** | 4" | 5.15 | 1.18 |

Full Product Series with Available Options Shown on Reverse Side

** 2 1/2" and larger are available only as malleable iron construction

GB0713.1



GB SERIES INDUSTRIAL SPECIFICATION GRADE
Set Screw, Threaded and Threadless Insulated Grounding Bushings
With and Without Optional Ground Lug

GB PRODUCT GROUP OPTIONS

| Trade Size | Material | Plating Options 1 | Configurations 2 | Insulated Throat Option 3 | Lug Options 4 | Lug Material Options 5 | Ground Lug Wire Range |
|------------|-------------|----------------------|---------------------|------------------------------|------------------|---------------------------|-----------------------|
| 1/2" | Solid Steel | Z or G | T - NT | Y | Y-N | AL - CU | 14-4 |
| 3/4" | Solid Steel | Z or G | T - NT | Y | Y-N | AL - CU | 14-4 |
| 1" | Solid Steel | Z or G | T - NT | Y | Y-N | AL - CU | 14-4 |
| 1 1/4" | Solid Steel | Z or G | T - NT | Y | Y-N | AL - CU | 14-4 or 8-10 |
| 1 1/2" | Solid Steel | Z or G | T - NT | Y | Y-N | AL - CU | 14-4 or 8-10 |
| 1 3/4" | Solid Steel | Z or G | T - NT | Y | Y-N | AL - CU | 14-4 or 8-10 |
| 2" | Solid Steel | Z or G | T - NT | Y | Y-N | AL - CU | 14-4 or 8-10 |
| 2 1/2" | MI | Z | T - NT | Y | Y-N | AL - CU | 6-250mcm |
| 3" | MI | Z | T - NT | Y | Y-N | AL - CU | 6-250 mcm |
| 3 1/2" | MI | Z | T - NT | Y | Y-N | AL - CU | 6-250 mcm |
| 4" | MI | Z | T - NT | Y | Y-N | AL - CU | 6-250 mcm |



Keys for Product Options Offered

- 1 Z = Zinc or G = Galvanized
- 2 T = Threaded NT = No Threads (Threadless with Set Screw)
- 3 Insulated Throat Option Available (B)
- 4 Available With and Without Ground Lug (GL)
- 5 AL = Aluminum Lug or CU = Copper Lug

For Full Part Numbers
 Go online: to amf.com/gbpn
 Or Call Factory

GB0713.1