

Steel Products

NEMA Enclosures

Weatherproof Products

Electrical Fittings

Wiring Devices

Exit & Emergency Lighting

Landscape Lighting

Line Voltage/HID Lighting

LED Lighting

Ventilation Fans

Cable & Wire

Industry Cross Reference

Newsletter

Sign Up Today!



T-75A

Be the first to review this product

TYPE T THREADED CONDUIT BODY 3/4" + CG

Download Spec Sheet

Email to a Friend

Print

Tweet



MORE VIEWS



Product Description

Additional Information

Product Tags

Category CONDUIT BODY

Page [D23](#)


Barcode 8-35243-00216-6

Features:

- Die Cast Copper-Free Aluminum
- With Die Cast Cover
- Neoprene Gasket

Dimension:

Dim A	1 - 9/16"
Dim B	4 - 11/16"
Dim C	1 - 5/8"
Dim D	5 - 1/2"
Dim E	2 - 5/16"



Specifications:

Color	Gray
Trade Size	3/4"

Packaging Info:

Std Pkg	10
Master Ctn	40

Certifications:



UL File Number:

[E227970](#)