

LED T8

L4T8E/835/15/F/G5

15 Watt LED Retrofit T8 Frosted

- Compatible with most electronic instant start, program start and emergency ballasts*
- Dimmable** Glass tube with PET coating is shatter resistant and NSF approved
- Extremely long life and energy efficient
- Contains no mercury



Item #	L4T8E/835/15/F/G5-70
Product Code	78020
UPC Code	751338001039
Watts	15
Volts	120-277
Lamp Shape	T8
Base	Med Bi-Pin
CRI	80
Color Temp	3500K
Initial Lumens	1,850
Beam Angle	240°
Average Rated Life	50,000
Ambient Temp Range	-4°F to 149°F
MOL	48"
Equivalent Wattage	32W T8
Warranty	5 years

Specifications are subject to change without prior notice.

* See ballast compatibility: www.topaz-usa.com/tools-resources/ballast-compatibility

**When used with dimmable fluorescent ballast

