



S9496

6.5MR16/LED/40°/30K/12V
 6.5 watt; LED MR16 LED; 3000K; 40° beam spread; GU5.3 base; 12 volt AC/DC

Features

- Silver back MR16 reflector
- Direct replacement for 50watt Halogen lamps
- Approved for enclosed fixtures
- Dimmable



S9496

Item Number	UPC	Voltage	Watts	Power Factor	Lamp Shape	Base	ANSI Base
S9496	045923094965	12v AC/DC	6.5	0.96	MR16	GU5.3	GU5.3

Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
6.5MR16/LED/40°/30K/12V	Dimmable	Compatible dimmers for S9496	Silver Back	1 3/4"	2"	500	25000

Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	ENERGY STAR	RoHS Compliant	UL or ETL Listed
3000	Warm White	80	40	12/48	ENERGY STAR	Yes	Yes

Warranty
3 Year Limited



National Toll-Free:
 800.43.SATCO
 (800.437.2826)
www.satco.com

Distribution Centers:
 New York, Florida, Texas,
 Washington, California,
 Puerto Rico

Corporate Offices:
 110 Heartland Blvd.,
 Brentwood, NY 11717
 800.437.2826 631.243.2022
 Fax 631.243.2027

